SIPA SFL 6-4



SIPA SFL Features

Flexible downstream

Accurate neck orientation

Vision System Inspection and

General Information

Technology: ISBM- 2-Step


Bottles can be hand packed in cartons or reshippers

during production along with in-line date coding

Can hold neck orientation to +/- 5° allow for consistent closure

Continual quality monitoring of bottles and wall thickness

Resins: PET Sizes: 1oz - 8L



- Preform Heating



• Capable of blowing a wide range of bottle styles and sizes Designed for maximum flexibility • Can run bottles with specialized neck finishes ranging from 28mm up to 48mm without support rings • Wide-mouth Capable • High Cavitation - suitable high volume franchises • Quick changeovers – normally 2-4 hours Low mold costs Blow molds = \$30,000 per set

SIPA SFL Benefits

Ideal Targets for Existing Preforms

Salad Dressing / Sauce	Size	Neck finish	Size	Neck Finish
	27.7 g	33-490	42.7 g	38-490
	35.9 g	33-490	49.0 g	38-490
	36.0 g	38-490	52.5 g	38-490
General Purpose	22.0 g	38-400	54.0 g	33-400
	27.7 g	33-400	72.5 g	38-400
	30.0 g	33-400	74.0 g	33-400
	35.9 g	33-400	83.0 g	33-400
	36.0 g	38-400	92.5 g	48-400
	47.0 g	33-400	129.0 g	48-400
	50.0 g	28-400		_

This is an internal Silgan Plastics only document and meant for basic reference only. For questions or pricing on specific projects, please contact the Plant, the appropriate Product Development Engineer or Technical Pricing Analyst.







